



Technisches Datenblatt

Schneider - Produkt : ILES 0,4 B – 980225T4

Dreiphasen - Drossel

Induktivität	:	2,0 mH
Nennstrom	:	16 A
Frequenz	:	150 Hz
Schaltgruppe	:	III
Schutzklasse	:	1
Schutzart	:	IP 00
Bauvorschrift	:	IEC 289
Isolationsklasse	:	ta 40/B
Umgebungstemperatur	:	0 - 40° C
Einschaltdauer	:	100 %
Kühlungsart	:	AN
Leerlaufverluste	:	ca. 20 W
Kupferverluste	:	ca. 35 W
max. Aufstellhöhe	:	<=1000 m über NN
Abmessungen	:	150 x 95 x 195 mm (L x B x H)
Gewicht	:	ca. 4,0 kg



Specification sheet

Schneider - product : ILES 0,4 B – 980225T4

three phase - choke

inductivity : 2,0 mH
 nominal current : 16 A
 frequency : 150 Hz
 vector group : III
 protection class : 1
 protective system : IP 00
 construction regulation : IEC 289
 insulation class : ta 40/B
 environmental temperature : 0 - 40° C
 operation duration : 100 %
 type of cooling : AN
 open circuit losses : app. 20 W
 copper losses : app. 35 W
 max. mounting height : <=1000 m above sea-level
 dimensions : 150 x 95 x 195 mm (L x B x H)
 weight : app. 4,0 kg