



REVISIONS			
REV	DESCRIPTION	DATE	APPROVED
1	INITIAL RELEASE		

- 003-3327-01
- 003-2734-01
- 003-3306-01
- 003-3177-01

LABEL CODE:  
 XX IS THE DASH NUMBER  
 DATE CODE IS DAY IT WAS MADE  
 EX: (082703)  
 -XX = LGTH IN METERS

CONNECTOR A

WIRE COLOR	FUNCTION	PIN #
RED	+5 to +24V DC	A
BLUE	NEGATIVE LIMIT	B
ORANGE	POSITIVE LIMIT	C
GREEN	HOME	D
BLACK	GROUND	E
SHIELD	SHIELD	Shield Case

CONNECTOR B

WIRE COLOR	FUNCTION	PIN #
RED	+5 to +24V DC	1
BLUE	NEGATIVE LIMIT	12
ORANGE	POSITIVE LIMIT	13
GREEN	HOME	14
BLACK	GROUND	15
SHIELD	SHIELD	Shield Case

<b>METRIC UNITS</b> ALL DIMENSIONS ARE IN MILLIMETERS (UNLESS OTHERWISE SPECIFIED)	ALL PARTS AND ASSEMBLIES TO BE MANUFACTURED PER PARKER HANNIFIN DAEDAL DIVISION PS1000 SPECIFICATIONS			
	STANDARD TOLERANCES, UNLESS OTHERWISE SPECIFIED		THE INFORMATION CONTAINED HEREIN IS BEING MADE AVAILABLE ONLY AS THE PROPERTY OF AND FOR THE PURPOSES OF PARKER HANNIFIN CORP. DAEDAL DIVISION. IT CANNOT BE LAWFULLY REPRODUCED IN ANY FORM NOR DIVULGED TO ANY THIRD PARTY, NOR USED FOR ANY PURPOSE OTHER THAN THAT WHICH IT HAS BEEN MADE AVAILABLE TO YOU WITHOUT THE EXPRESS WRITTEN CONSENT OF PARKER HANNIFIN DAEDAL DIVISION	
ALL THREADS TO BE: I.S.O. 4g6g OR 4H6H (COARSE PITCH)	DECIMALS .X ±.2 .XX ±.10 .XXX ±.010	RMS FINISH 1600/√	ANGLES ±0°30'	
REFERENCE DRAWINGS	CHAMFERS: 45° x .5    RADII: .5 R.	DRAWN <b>OPEL</b> 5/12/08	<b>LIMIT/HOME CABLE          COMPAX CONN</b>	
ASSY or NSPER No.:	REMOVE BURRS, BREAK SHARP EDGES	CHECKED	Manual & Motorized Positioning Systems	
SALES ORDER No.:	MATERIAL <b>N/A</b>	DESIGN	AutoCad <b>B</b> <b>006-2163</b> DRAWING	
FILE NAME:	FINISH <b>N/A</b>	ENGINEERING	SCALE: <b>N/A</b> REPRO:    SHT. 1 OF 1    REV. 1	
MADE FROM(FILE): 006-1891		MANUFACTURING		
		QUALITY ASSURANCE		
		ASSEMBLY		